FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M20X70

Article number	04105.200.070
Brand	-
UBB	500505564509
UNSPSC	31161620
EAN	8715494439626
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	70 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	70
P	2.5

Technical Drawing

