FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M24X130

Article number	04105.240.130
Brand	-
UBB	500644690132
UNSPSC	31161620
EAN	8717077017900
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	130 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	130
P	3

Technical Drawing

