FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M24X140

Article number	04105.240.140
Brand	-
UBB	500505565753
UNSPSC	31161620
EAN	8715494440615
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	140 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	140
P	3

Technical Drawing

