FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M10X60

Article number	04108.100.060
Brand	-
UBB	955351408427
UNSPSC	31161620
EAN	8715493849648
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	60
P	1.5
s	17

Technical Drawing

