FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M12X90

Article number	04108.120.090
Brand	-
UBB	955351409417
UNSPSC	31161620
EAN	8715493849747
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	90 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	90
P	1.75
s	19

Technical Drawing

