FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M16X130

Article number	04108.160.130
Brand	-
UBB	955351411215
UNSPSC	31161620
EAN	8715493849921
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	130 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	130
P	2
s	24

Technical Drawing

