FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M16X140

Article number	04108.160.140
Brand	-
UBB	955351411397
UNSPSC	31161620
EAN	8715493849938
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	140 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	140
P	2
s	24

Technical Drawing

