FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M20X140

Article number	04108.200.140
Brand	-
UBB	955351412049
UNSPSC	31161620
EAN	8715493850002
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	140 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	140
P	2.5
s	30

Technical Drawing

