FABORY

Hexagon head bolt DIN 931 Steel Plain 12.9 M24X100

Article number	04108.240.100
Brand	-
UBB	955351412387
UNSPSC	31161620
EAN	8715493850033
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	100 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	100
P	3
s	36

Technical Drawing

