
FABORY



Hexagon flange bolt DIN 6921 Steel Zinc plated 10.9 M10X50

Article number	04137.100.050
Brand	-
UBB	500648944915
UNSPSC	31161620
EAN	8717077238626
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.Specific features of hexagon bolts with flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

ASME	≈B18.2.3.4M
DIN	6921
EN	≈1665
ISO	≈4162

Technical Specification

b (min.)	26
d-D	M10
dc (max.)	22.3
k (max.)	9.2
L (mm)	50
P	1.5
s	15

Technical Drawing

