
FABORY



Hexagon flange bolt EN 1665 Steel Zinc plated 10.9 M6X25

Article number	04140.060.025
Brand	-
UBB	500650800096
UNSPSC	31162400
EAN	8717077294455
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	25 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921
ASME	≈B18.2.3.4M
EN	1665
ISO	≈4162

Technical Specification

b (min.)	18
d-D	M6
dc (max.)	14.2
k (max.)	6.6
L (mm)	25
P	1
s	10

Technical Drawing

