
FABORY



Hexagon flange bolt EN 1665 Steel Zinc plated 10.9 M12X80

Article number	04140.120.080
Brand	-
UBB	500650802316
UNSPSC	31162400
EAN	8717077294684
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921
EN	1665
ISO	≈4162
ASME	≈B18.2.3.4M

Technical Specification

b (min.)	30
d-D	M12
dc (max.)	26.6
k (max.)	11.8
L (mm)	80
P	1.75
s	18

Technical Drawing

