
FABORY



Hexagon flange bolt EN 1665 Steel Zinc plated 10.9 M16X35

Article number	04140.160.035
Brand	-
UBB	500650802498
UNSPSC	31162400
EAN	8717077294691
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	35 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	≈4162
ASME	≈B18.2.3.4M
DIN	≈6921
EN	1665

Technical Specification

b (min.)	38
d-D	M16
dc (max.)	35
k (max.)	15.4
L (mm)	35
P	2
s	24

Technical Drawing

