FABORY



Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M12X1,25X70

Article number	04161.120.070
Brand	-
UBB	500645030767
UNSPSC	31161620
EAN	8717077052710
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	70 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-152
ISO	8765
NEN	1555
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	70
P	1.25

Technical Drawing

