FABORY

# Hexagon nut DIN 934 Steel Plain |12| M12

| | |
|---|---|
| Article number | 04190.120.001 |
| Brand | - |
| UBB | 950355327046 |
| UNSPSC | 31161727 |
| EAN | 8715492123145 |
| PKG. of 100 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M12 |
| Class | \|12\| |
| Driving features | Hexagon |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| DIN | 934 |
| NF | E25-401 |
| NEN | 1560 |

## Technical Specification

| | |
|---|---|
| d-D | M12 |
| m | 10 |
| P | 1.75 |
| s | 19 |

## Technical Drawing

