FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M16X360

Article number	07015.160.360
Brand	-
UBB	500644747577
UNSPSC	31161605
EAN	8717077023307
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M16
Length	360 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-125
ISO	4762
BS	4168-1
NEN	1241
ASME	B18.3.1M
DIN	912

Technical Specification

b	44
d-D	M16
dk (max.)	24
Full thread if L ≤	60
k (max.)	16
L (mm)	360
P	2
s	14

Technical Drawing

