FABORY



# Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M6X20

| | |
|---|---|
| Article number | 07023.060.020 |
| Brand | - |
| UBB | 500647940146 |
| UNSPSC | 31161605 |
| EAN | 8717077282032 |
| PKG. of 500 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M6 |
| Length | 20 mm |
| Class | 10.9 |
| Driving features | Hexagon socket |
| Head shape | Cylindrical head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

## Standards

| | |
|---|---|
| BS | 4168-1 |
| ASME | B18.3.1M |
| NEN | 1241 |
| NF | E25-125 |
| DIN | 912 |
| ISO | 4762 |

## Technical Specification

| | |
|---|---|
| b | 24 |
| d-D | M6 |
| dk (max.) | 10 |
| Full thread if L ≤ | 30 |
| k (max.) | 6 |
| L (mm) | 20 |
| P | 1 |
| s | 5 |

## Technical Drawing

