FABORY



# Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M14X60

| | |
|---|---|
| Article number | 07023.140.060 |
| Brand | - |
| UBB | 500647953180 |
| UNSPSC | 31161605 |
| EAN | 8717077283336 |
| PKG. of 50 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M14 |
| Length | 60 mm |
| Class | 10.9 |
| Driving features | Hexagon socket |
| Head shape | Cylindrical head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

## Standards

| | |
|---|---|
| DIN | 912 |
| BS | 4168-1 |
| ASME | B18.3.1M |
| ISO | 4762 |
| NF | E25-125 |
| NEN | 1241 |

## Technical Specification

| | |
|---|---|
| b | 40 |
| d-D | M14 |
| dk (max.) | 21 |
| Full thread if L ≤ | 55 |
| k (max.) | 14 |
| L (mm) | 60 |
| P | 2 |
| s | 12 |

## Technical Drawing

