FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M14X65

Article number	07023.140.065
Brand	-
UBB	500647953263
UNSPSC	31161605
EAN	8717077283343
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	65 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	4762
ASME	B18.3.1M
NF	E25-125
DIN	912
NEN	1241
BS	4168-1

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if L ≤	55
k (max.)	14
L (mm)	65
P	2
s	12

Technical Drawing

