FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M16X140

Article number	07023.160.140
Brand	-
UBB	500647956076
UNSPSC	31161605
EAN	8717077283626
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	140 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	912
BS	4168-1
ASME	B18.3.1M
NEN	1241
NF	E25-125
ISO	4762

Technical Specification

b	44
d-D	M16
dk (max.)	24
Full thread if L ≤	60
k (max.)	16
L (mm)	140
P	2
s	14

Technical Drawing

