FABORY



# Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M18X55

| | |
|---|---|
| Article number | 07060.180.055 |
| Brand | - |
| UBB | 950351415555 |
| UNSPSC | 31161605 |
| EAN | 8715492058508 |
| PKG. of 25 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M18 |
| Length | 55 mm |
| Class | 8.8 |
| Driving features | Hexagon socket |
| Head shape | Cylindrical head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ISO | 4762 |
| NF | E25-125 |
| NEN | 1241 |
| BS | 4168-1 |
| DIN | 912 |
| ASME | B18.3.1M |

## Technical Specification

| | |
|---|---|
| b | 48 |
| d-D | M18 |
| dk (max.) | 27 |
| Full thread if L ≤ | 65 |
| k (max.) | 18 |
| L (mm) | 55 |
| P | 2.5 |
| s | 14 |

## Technical Drawing

