FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M20X90

Article number	07060.200.090
Brand	-
UBB	950351417460
UNSPSC	31161605
EAN	8715492058805
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	90 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	912
ASME	B18.3.1M
NEN	1241
BS	4168-1
ISO	4762
NF	E25-125

Technical Specification

b	52
d-D	M20
dk (max.)	30
Full thread if L ≤	75
k (max.)	20
L (mm)	90
P	2.5
s	17

Technical Drawing

