FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M24X280

Article number	07060.240.280
Brand	-
UBB	952351351269
UNSPSC	31161605
EAN	8715492059567
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	280 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	912
ASME	B18.3.1M
ISO	4762
NF	E25-125
BS	4168-1
NEN	1241

Technical Specification

b	60
d-D	M24
dk (max.)	36
Full thread if L ≤	85
k (max.)	24
L (mm)	280
P	3
s	19

Technical Drawing

