FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M36X120

Article number	07060.360.120
Brand	-
UBB	952351356474
UNSPSC	31161605
EAN	8715492060273
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Length	120 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-125
ASME	B18.3.1M
BS	4168-1
ISO	4762
DIN	912
NEN	1241

Technical Specification

b	84
d-D	M36
dk (max.)	54
Full thread if L ≤	110
k (max.)	36
L (mm)	120
P	4
s	27

Technical Drawing

