FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M3X12

Article number	07065.030.012
Brand	-
UBB	500577359093
UNSPSC	31161605
EAN	8715494328753
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4762
DIN	912
NEN	1241
NF	E25-125
ASME	B18.3.1M
BS	4168-1

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	12
P	0.5
s	2.5

Technical Drawing

