FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M3X16

Article number	07065.030.016
Brand	-
UBB	500577359176
UNSPSC	31161605
EAN	8715494328760
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	16 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.3.1M
DIN	912
NEN	1241
NF	E25-125
BS	4168-1
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	16
P	0.5
s	2.5

Technical Drawing

