FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M5X10

Article number	07065.050.010
Brand	-
UBB	500577360224
UNSPSC	31161605
EAN	8715494328876
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	10 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

BS	4168-1
ISO	4762
DIN	912
ASME	B18.3.1M
NF	E25-125
NEN	1241

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if L ≤	25
k (max.)	5
L (mm)	10
P	0.8
s	4

Technical Drawing

