FABORY



Hexagon socket head cap screw with low head DIN 7984 Steel Zinc plated 08.8 M5X14

Article number	07090.050.014
Brand	-
UBB	500645086611
UNSPSC	31161605
EAN	8717077058545
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	14 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

DIN	7984

or with the steel grade only, e.g. 'A2'.

FABORY

Technical Specification

b (min.)	16
d-D	M5
dk	8.5
Full thread if L ≤	25
k	3.5
L (mm)	14
P	0.8
s	3

Technical Drawing

