FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M3X6

Article number	07160.030.006
Brand	-
UBB	950351440629
UNSPSC	31161605
EAN	8715492070746
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-125
DIN	912
BS	4168-1
NEN	1241
ASME	B18.3.1M
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	6
P	0.5
s	2.5

Technical Drawing

