FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M5X110

Article number	07160.050.110
Brand	-
UBB	500645095372
UNSPSC	31161605
EAN	8717077059412
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	110 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	912
BS	4168-1
NEN	1241
ISO	4762
NF	E25-125
ASME	B18.3.1M

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if L ≤	25
k (max.)	5
L (mm)	110
P	0.8
s	4

Technical Drawing

