FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M12X200

Article number	07160.120.200
Brand	-
UBB	500645103291
UNSPSC	31161605
EAN	8717077060203
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	200 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-125
ASME	B18.3.1M
BS	4168-1
NEN	1241
DIN	912
ISO	4762

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if L ≤	50
k (max.)	12
L (mm)	200
P	1.75
s	10

Technical Drawing

