FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M14X130

Article number	07160.140.130
Brand	-
UBB	500645103606
UNSPSC	31161605
EAN	8717077060241
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	130 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	4168-1
ASME	B18.3.1M
NEN	1241
NF	E25-125
ISO	4762
DIN	912

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if L ≤	55
k (max.)	14
L (mm)	130
P	2
s	12

Technical Drawing

