
FABORY



Hexalobular socket head cap screw ISO 14579 Steel Zinc plated 8.8 M6X35

Article number	07165.060.035
Brand	-
UBB	500504704213
UNSPSC	31161605
EAN	8715494194051
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	35 mm
Class	8.8
Driving features	Hexalobular
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	14579

Technical Specification

b	24
d-D	M6
dk (max.)	10
Full thread if L ≤	30
k (max.)	6
L (mm)	35
P	1
Socket	30

Technical Drawing

