FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated yellow passivated 8.8 M3X8

Article number	07170.030.008
Brand	-
UBB	954351403553
UNSPSC	31161605
EAN	8715492073594
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.3.1M
BS	4168-1
NF	E25-125
NEN	1241
DIN	912
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	8
P	0.5
s	2.5

Technical Drawing

