FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated yellow passivated 8.8 M5X8

Article number	07170.050.008
Brand	-
UBB	500645105270
UNSPSC	31161605
EAN	8717077060401
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4762
DIN	912
BS	4168-1
ASME	B18.3.1M
NF	E25-125
NEN	1241

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if L ≤	25
k (max.)	5
L (mm)	8
P	0.8
s	4

Technical Drawing

