
FABORY



Flat countersunk nib bolt with hexagon nut DIN 604/555 Steel Plain 4.6 M16X130

Article number	08070.160.130
Brand	-
UBB	500644845330
UNSPSC	31161612
EAN	8717077033085
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	130 mm
Class	4.6
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.


Standards

DIN	604/555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
dk (max.)	32.8
g (max.)	4.2
k	9
L (mm)	130
m	13

Technical Drawing



P	2
s	24
α (min.)	90