
FABORY



Flat countersunk nib bolt with hexagon nut DIN 604/555 Steel Plain 4.6 M24X65

Article number	08070.240.065
Brand	-
UBB	500644846163
UNSPSC	31161612
EAN	8717077033160
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Length	65 mm
Class	4.6
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.


Standards

DIN	604/555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
dk (max.)	38.8
g (max.)	6.6
k	13
L (mm)	65
m	19

Technical Drawing



P	3
s	36
α (min.)	60