
FABORY



Carriage bolt DIN 603 Steel Plain 8.8 M6X30

Article number	08310.060.030
Brand	-
UBB	950351617101
UNSPSC	31161612
EAN	8715492558244
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Threaded pitch (P)	1
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	≈303
BS	≈4933
ISO	≈8677
DIN	603

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
dk (max.)	16.55
k (max.)	3.88
L (mm)	30
P	1
fn (max.)	4.6
Vn (max.)	6.48

Technical Drawing

