
FABORY



Carriage bolt DIN 603 Steel Plain 8.8 M8X35

Article number	08310.080.035
Brand	-
UBB	950351618018
UNSPSC	31161612
EAN	8715492558336
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Threaded pitch (P)	1.25
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	603
NEN	≈303
ISO	≈8677
BS	≈4933

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L200mm	41
b (min.): L≤125mm	22
d-D	M8
dk (max.)	20.65
k (max.)	4.88
L (mm)	35
P	1.25
fn (max.)	5.6
Vn (max.)	8.58

Technical Drawing

