
FABORY



Carriage bolt DIN 603 Steel Zinc plated 8.8 M8X80

Article number	08320.080.080
Brand	-
UBB	500645159715
UNSPSC	31161612
EAN	8717077066601
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	80 mm
Threaded pitch (P)	1.25
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈303
BS	≈4933
ISO	≈8677
DIN	603

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L200mm	41
b (min.): L≤125mm	22
d-D	M8
dk (max.)	20.65
k (max.)	4.88
L (mm)	80
P	1.25
fn (max.)	5.6
Vn (max.)	8.58

Technical Drawing

