
FABORY



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |5| M20

Article number	12300.200.001
Brand	-
UBB	950355116662
UNSPSC	31161727
EAN	8715492576927
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Class	|5|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	985
ISO	≈10511
NF	E25-412

Technical Specification

d-D	M20
h	20
P	2.5
s	30

Technical Drawing

