
FABORY



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |8| M16

Article number	12348.160.001
Brand	-
UBB	951355382478
UNSPSC	31161727
EAN	8715493855724
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Class	|8|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-412
DIN	985
ISO	≈10511

Technical Specification

d-D	M16
h	16
P	2
s	24

Technical Drawing

