
FABORY



BILOC Prevailing torque type hexagon nut, all metal DIN ≈980V Steel Zinc plated 8 M10

Article number	12385.100.001
Brand	-
UBB	500650968646
UNSPSC	31162400
EAN	8717077311398
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7042
DIN	≈980-V

Technical Specification

d-D	M10
m (max.)	8.4
P	1.5
s	17

Technical Drawing

