
FABORY



# Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |10| M6

| | |
|---|---|
| Article number | 12410.060.001 |
| Brand | - |
| UBB | 950355542602 |
| UNSPSC | 31161727 |
| EAN | 8715492578495 |
| PKG. of 250 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M6 |
| Class | \|10\| |
| Driving features | Hexagon |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ISO | ≈10511 |
| NF | E25-412 |
| DIN | 985 |

## Technical Specification

| | |
|---|---|
| d-D | M6 |
| h | 6 |
| P | 1 |
| s | 10 |

## Technical Drawing

