
FABORY



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |10| M8

Article number	12410.080.001
Brand	-
UBB	950355542784
UNSPSC	31161727
EAN	8715492578501
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Class	|10|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-412
DIN	985
ISO	≈10511

Technical Specification

d-D	M8
h	8
P	1.25
s	13

Technical Drawing

