
FABORY



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |10| M18

Article number	12410.180.001
Brand	-
UBB	950355663713
UNSPSC	31161727
EAN	8715492578556
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M18
Class	|10|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈10511
NF	E25-412
DIN	985

Technical Specification

d-D	M18
h	18.5
P	2.5
s	27

Technical Drawing

