
FABORY



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |10| M22

Article number	12410.220.001
Brand	-
UBB	950355768835
UNSPSC	31161727
EAN	8715492578570
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M22
Class	|10|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-412
DIN	985
ISO	≈10511

Technical Specification

d-D	M22
h	22
P	2.5
s	32

Technical Drawing

