FABORY



Prevailing torque type hexagon nut with flange all metal EN 1664 Steel Zinc plated 8 M10

Article number	12465.100.001
Brand	-
UBB	500650971285
UNSPSC	31162400
EAN	8717077311657
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

EN	1664

Technical Specification

d-D	M10
dc	21.8
h	11.4
m (js15)	9.6
P	1.5
s	16

Technical Drawing

