
FABORY



Prevailing torque type hexagon nut with plastic insert, high type ISO 7040 Steel Zinc plated 8 M10

Article number	12510.100.001
Brand	-
UBB	500650979122
UNSPSC	31162400
EAN	8717077312449
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	7040
DIN	6924

Technical Specification

d-D	M10
h (max.)	11.9
P	1.5
s	16

Technical Drawing

