
FABORY



Prevailing torque type hexagon nut with plastic insert, high type ISO 7040 Steel Zinc plated 8 M16

Article number	12510.160.001
Brand	-
UBB	500650979460
UNSPSC	31162400
EAN	8717077312470
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	6924
ISO	7040

Technical Specification

d-D	M16
h (max.)	19.1
P	2
s	24

Technical Drawing

